

高溫燒機老化試驗房 High Temperature Aging Test Room



產品用途:

高溫燒機老化試驗房,實驗各種材料耐熱,耐寒,耐幹,耐潔性能。適合電子,電器,通訊,儀表,車輛,塑膠製品,金屬, 食品,化學,建材,醫療,航太等大型試驗樣品檢測質量之用。

Application:

High Temperature Aging Test Room is used to test various types of materials for their tolerances of heat, cold, dry, humidity. It is applied for quality inspection for all types of big test samples, such as electronic products, electric appliance, and products from communication, instrument, automobile, plastic, metal, food, chemical, building materials, medical and aerospace industries.

特點

- ●質感外觀,機體採用圓弧造型,表面經霧面條紋處理,並採用平面無反作用把手,操作容易,安全可靠。
- ●長方形復層玻璃觀視窗,可在實驗中進行試驗品觀察使用,視窗具防汗電熱器裝置可防止水氣凝結水滴,及高亮度PL熒光燈保持箱内照明。
- 箱門雙層隔絕氣密迫緊,可有效隔絕內部溫度洩露。
- ●壓縮機循環系統採用法國"泰康"牌,更能有效去除冷凝管與毛細管間的潤滑油並全系列採用環保冷媒(R22,R404)。
- ●控制器採用進口LCD顯示螢幕,可同時顯示測定值及設定值、時間。
- ●控制器具有多段程式編輯及溫度、可做快速 (OUICK)或斜率 (SLOP)控制
- ●内置式移動滑輪便於移動及擺放並具有強力定位螺絲固定位置。

Features:

- •Graceful appearance, circularly shaped body, surface treated with mist strips and plane handle with no reaction. Easy to operate, safe and reliable.
- •Rectangular double-glassed watching window for the observation of the test production during the testing process.
 The window is equipped with sweat-proof electrical heating device that can prevent water steam from condensing into droplets, and with high brightness PL fluorescent bulbs to provide light inside the box.
- Water supply system that is externally connectable, convenient for refilling water into the humidifying pot and automatically recyclable.
- •The French "Tecumseh" brand is used for the circulation system of the compressor, capable of removing the lubricant between the condensation pipes and capillaries. The environment-protecting coolant is used for the whole series(R22,R404)
- •Imported LCD display screen, capable of displaying the measured value as well as the set value and time.

 The control unit has the functions of multiples segment program editing, and of quick or slope control of temperature.
- •Inserted mobile pulley, convenient for movement a relocation, with strong positioning screws.

技術參數Technical Parameters:

| 型號 Model | TAR-容積 TAR-volume |
|---|--|
| 内尺寸W×H×D (mm) Inner Dimensions W×H×D (mm) | 根據客戶制定的尺寸大小而設計 Customers designated space size and design |
| 溫度範囲 Temperature Range | (RT+15℃)~80℃;(80℃ ~150℃為特殊週期型) (RT+15℃)~80℃;(80℃ ~150℃ is optional) |
| 溫度解析糟度/分佈均勻度 Analytic Accuracy/Distribution Uniformity of Temperature | 0.1℃ ±3.5℃ |
| 溫度控制精度 Control Accuracy of Temperature | ±0.5℃; |
| 升溫速率 Temperature Rising Speed Rate | 升温速率約0.1~3.0℃/分鐘; Temperature rising speed: approx. 0.1~3.0℃/min |
| 冷卻系統 Cooling System | 壓縮機製冷,根據用戶的需求配置 Refrigeration by compressor, according to customer's requirements |
| 保護裝置 ProtectionDevices | 無熔絲開闢、壓縮機過載保護開闢、冷煤高低壓保護開闢、超溫保護開闢、保險 絲、故障警告系統 Fuse-free switch, overloading protection switch for compressor, high and low voltage coolant protection switch, over- temperature protection switch, fuses, fault warning system |
| 選購配件 / Optional Accessories | 推車斜坡、 記錄器 Slope for cart , Recorder |
| 壓縮機 Compressor | 法國"泰康"牌;德國"比則爾" French "Tecumseh" Brand,Germany "Bizer" Brand |
| 電源 / Power | AC380V; 3∮ 5線; 50/60HZ AC380V; 3∮ 5 Lines; 50/60HZ |
| | |